

P-ONE Optical Module production

Tuesday, 26 May 2026 12:15 (15 minutes)

We use 3 inch PMTs from Hamamatsu. The PMTs are optically coupled to the glass with individual gel pads. Additionally, a spring-loaded system presses them against the glass and holds them in place. The GNN collaboration could benefit from this talk by discussing new ideas and developments for optical module design and production.

Primary author: WINTER, Laura (TUM)

Presenter: WINTER, Laura (TUM)

Session Classification: Topical Sessions

Track Classification: Detectors and Devices